

## Features

- 3.5 mm pitch
- Voltage Rating: 300V
- Current Rating: 8A
- Low Mating Force
- 2 WAY HEADER  
VERTICAL  
TERMINAL

## RS PRO 3.5MM PITCH 2 WAY, 8A, HEADER VERTICAL TERMINAL

RS Stock No.: 0631104



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

**Product Description**

- Vertical mount closed end PCB terminal block headers with a 3.5mm pitch. These 3.5mm pluggable terminal block PCB header connectors have a 300V 8A electrical rating and have green PA66 housings

**General Specifications**

Number of Contacts	2
Number of Rows	1
Pitch	3.5mm
Mounting Type	Through Hole
Body Orientation	Straight
Number of P	2
Termination Method	Solder
Contact Material	Brass
Contact Plating	Tin plated
Housing	PA66(UL94V-0)
Colour	Green

**Electrical Specifications**

Voltage Rating	300V
Current Rating	8A
Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

## Mechanical Specifications

Mounting Type	Through Hole
Pitch	3.5 mm
Pin size	Please see below drawings
Pin height	3.5mm

## Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

## Approvals

Compliance/Certifications	RoHS Compliant, UL, CE
Declarations	Reach

## Spec Drawings



