

Eaton 248438

Catalog Number: 248438

Eaton Distribution parts. Shunt release, snap-fit, 12-110V AC / 12-60V DC, 50/60hz, front dimension 45 mm, mounting width 1 SU (17.5mm), top-hat rail mounting, terminal cross-section 1–25 mm²



General specifications

Product Name	Catalog Number
Eaton Distribution parts	248438
EAN	Product Length/Depth
4015082484385	80 mm
Product Height	Product Width
75 mm	26.2 mm
Product Weight	Compliances
0.087 kg	RoHS conform
Certifications	
EN45545-2	
IEC 61373	

Product specifications

Used with

Shunt releases

Accessory

Accessory for combined residual current/power circuit breaker

Accessory for miniature circuit breaker

Type

Accessory

Accessory for combined

residual current/power

circuit breaker

Accessory for miniature

circuit breaker

Application

Switchgear for industrial and advanced commercial applications

Accessory/spare part type

Shunt release

Mounting method

For fitting on left to: FAZ, FRBmM-1N, Z-MS

Additional equipment required

Shunt release (for power circuit breaker)

Ambient operating temperature - max

75 °C

Ambient operating temperature - min

-35 °C

Assembly width

1 TE

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

1

Number of contacts (normally open contacts)

1

Number of poles at main contact unit - max

1

Number of switches (fault signal)

0

Resources

Declarations of conformity

[DA-DC-03_ZP-ASA](#)

[DA-DC-03_ZP-A](#)

Drawings

[eaton-3d-drawing-mont-usa-2.jpg](#)

[eaton-3d-drawing-zp-asa-mont.jpg](#)

[eaton-dimensions-mas-zp-asa.jpg](#)

eCAD model

[ETN.ZP-ASA_24.edz](#)

Installation instructions

[IL019163ZU](#)

mCAD model

[faz_xaa.stp](#)

[faz_xaa.dwg](#)

Wiring diagrams

[eaton-wiring-diagram-asa.jpg](#)

Voltage type

AC

Functions

Shunt release (for power circuit breaker)

Device fitting

Other

Rated operational voltage (Ue) - max

24 V

Rated switch current

0 A

Suitable for current of main contact unit - max

15 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia