

**Product Family****CSM Glovebox Gloves -
10Y1532A**

CSM Glovebox Gloves. Outstanding abrasion resistance. Superior resistance to ozone or oxidizing chemicals. Naturally soft for greater worker comfort. White surface for good visibility; will not hide contamination. Hand specific or ambidextrous, available in a variety of port diameters and sizes.

logo_North

Overview**Key Features**

CSM Glovebox Gloves. Outstanding abrasion resistance. Superior resistance to ozone or oxidizing chemicals. Naturally soft for greater worker comfort. White surface for good visibility; will not hide contamination. Hand specific or ambidextrous, available in a variety of port diameters and sizes.

Regulations

- ANSI/ISEA 105 - ASTM D3389-05 Abrasion Test
- ANSI/ISEA 105 - ASTM D412 - Physical properties
- ANSI/ISEA 105 - ASTM F1790-97 Cut Test
- EN374 - Permeation and breakthrough time
- EN388 - Mechanical risks from abrasion, cut, tear and puncture
- EN420 - General Requirements - This standard defines the general requirements for protective gloves in terms of construction, fitness of purpose and safety.
- OSHA Standard -29 CFR 1915.157 - The employer shall ensure that each affected employee uses appropriate hand protection and other protective clothing where there is exposure to hazards such as skin absorption of harmful substances, severe cuts or lacerations, severe abrasions, punctures, chemical burns, thermal burns, harmful temperature extremes, and sharp objects.

Warranty Information

LIMITED WARRANTY. Except for any warranty for a particular product or part specifically stated in our product literature, we warrant all goods sold under this agreement against defects in materials and workmanship for one year from shipment. In the event of such defects, we will, at our sole option and as your exclusive remedy, repair or replace the defective product without charge, or refund the price you have paid. In order for this warranty to be effective, you must notify us within 15 days of discovery of the defect. you must return the defective product to us within the warranty period, properly packaged and with insurance and transportation costs prepaid. We will reship the product to you at our expense in the United States. Products will conform to Honeywell published specifications if properly used and maintained and will be free from defects in materials and/or workmanship. no changes to Honeywell published specifications will be valid without Honeywell written consent. This warranty does not cover defects which we determine are because of accident, alteration, modification, negligence, misuse, abuse failure to perform adequate maintenance, or normal wear and tear.

Specifications**Ambidextrous or Hand Specific**

- Ambidextrous

Coating

- NA

Coating Color

- NA

Coating Pattern

- NA

Construction

- Multi-Dip

Cuff

- NA

Gauge / mil

- 15 mil

Glove Type

- Glovebox glove

Length

- 32 inch

Liner

- None

Material

- Chlorosulfonated Polyethylene

Material Color

- White

Overedge

- NA

Supported or Unsupported

- Unsupported

Surface Finish

- Smooth

Literature & Documents

2602_pdf

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Gloves/19327356557/1033.aspx

! "#\$%&'()*+,-./:;<=>?@A B C D E F G H I J K L M N O P Q R S T U V W X Y Z [\] ^ _ ` { | } ~ ¡ ¢ £ ¤ ¥ ¦ § ¨ © ª « ¬ ® ¯ ° ± ² ³ ´ µ ¶ · ¸ ¹ º » ¼ ½ ¾ ¿ À Á Â Ã Ä Å Æ Ç È É Ê Ë Ì Í Î Ï Ñ Ò Ó Ô Õ Ö × Ø Ù Ú Û Ü Ý Þ à á â ã ä å æ ç è é ê ë ì í î ï ð ñ ò ó ô õ ö ÷ ø ù ú û ü ý þ ÿ

2603_pdf

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Gloves/19327356558/1033.aspx

EC DECLARATION OF CONFORMITY The company: North Safety Products Europe bv P.O. Box 5016 4330 KA, Middelburg The Netherlands Declares that the safety product described below: Drybox gloves made from Hypalon Articles: Port sizes: 5,6,7,8,10 inch Thickness: 15 and 32 mil Ambidextrous and hand specific Different lengths Ar

Technical Support

Technical Support is available Monday through Friday, 8:00 AM to 7:00 PM EST. 1.800.873.5242
hsptechsupport@honeywell.com