

AB810 - Nitrosafe Essential Multipack (PK12)

Collection: Chemical Protection Gloves

Range: Hand Protection

Materials: Nitrile, Cotton

Outer Carton: 16

Product information

Experience superior grip and protection with our chemical-resistant gauntlet, featuring a textured pattern that enhances grip in wet or oily conditions. Flock-lined for added comfort, this gauntlet is suitable for use in chemical, oil, and food industries. This gauntlet is a streamlined version of our flagship A810 gauntlet, without individual packaging, making it a more economical choice. Sold in packs of 12 for maximum value.

Chemical Protection Gloves

Working environments using hazardous chemicals and substances can be extremely harmful to workers and the correct protection is a must. Portwest supplies a range of gloves which are fully tested and certified to protect from a range of chemicals.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5
EN 388: 2016 + A1: 2018 (3101X)
EN ISO 374-1:2016 + A1:2018 Type B (JKL)
EN ISO 374-5:2016 Micro Organisms



Features

- Sold in pack of 12 pairs for great value
- Chemical resistant gauntlet
- Flock lined for added comfort
- Textured palm
- 0.40mm thickness
- 320mm length
- CE certified
- UKCA marked
- New style



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

AB810 - Nitrosafe Essential Multipack (PK12)
Commodity Code: 4015190000

Test House

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
AB810GNRS	Green	37.0	32.0	37.0	0.7240	0.0438	5036146018925	15036108894120
AB810GNRM	Green	37.0	32.0	37.0	0.7720	0.0438	5036146018918	15036108894113
AB810GNRL	Green	37.0	32.0	37.0	0.9700	0.0438	5036146018901	15036108894106
AB810GNRXL	Green	37.0	32.0	37.0	0.9350	0.0438	5036146018932	15036108894137
AB810GNRXXL	Green	37.0	32.0	37.0	0.9290	0.0438	5036146018949	15036108894144