

# DOUBLE FLEX WRENCH METRIC 10 X 11MM



- Swivel end wrench for fast pre-tightening and loosening
- 12 point socket at each end with 2 different sizes in one wrench
- Angle at 90° for added torque when applying the final tightening
- Extra torque for loosening stubborn fastenings
- Chrome vanadium satin finish
- Designed and manufactured to DIN standards

Double Flex Wrench 10x11mm

## General information

**Country of origin:** Taiwan  
**Barcode:** 5020385040236  
**Tariff code Europe:** 8204110000  
**ECCN US:** EAR99  
**ETIM:** EC011818  
**UNSPSC:** 27111705

## Dimensions

**Net weight (g):** 106  
**Length:** 200 mm

## Attributes

**Product type:** Double Flex Wrenches  
**Material:** CrV  
**Certificates:** N/A  
**Size:** 10 × 11 mm  
**Flexible head:** Yes  
**Tethering facility:** Yes  
**Unit of measurement:** Metric

## Features



 **DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.

Technical changes and errors may occur. 01-08-2024 19:49



Sandbergsvägen 3  
441 39 Alingsås, Sweden