
Batteries

DATA SHEET

NO MERCURY ADDED			
Description	Mercury & Cadmium Free Alkaline Manganese Battery, AAA Size		
Chemical System	Alkaline Manganese		
Nominal Voltage	1.5 Volts		
Nominal Dimensions	Refer to drawing		
Terminals	Protruded positive (+) and flat negative (-) contacts		
Jacket	Foil jacket		
Applications	Internet of Things (IoT), sensors, home security products, smart remote control, wireless mouse/keyboard, toys, smart meters, medical/smart healthcare, thermometers, dispensers.		
Ambient Temperature Range	Operation: -18°C ~ 50°C Recommended: 10°C ~ 25°C Storage: Not exceed 30°C		
Shelf Life	10 years		
Approx. Weight	12.0g		


Cross References:					
GP	JIS	IEC	Energizer	Duracell	Varta
24AUP	LR03	LR03	E92	MX2400	4003

Discharge curve:



- **Hemarks**1) Store period before test shall be under 20±2°C, RH 55±20% within 30 days of manufacture.
 2) Batteries shall not leak during the service life test before the end voltage reached.

Ultra+ Model No.: GP24AUP



/	min	max		
Ø	9.8	10.5		
Α	43.5	44.5		
С	4.3	_		
F	_	3.8		
G	0.8	_		
Dimension : mm				

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

ē