

M18 RLOHVG300-501C

M18™ 300 M GREEN HORIZONTAL VERTICAL ROTARY LASER WITH ONE-KEY™

- Designed for interior and exterior jobs, for long distance applications
- Automatic centre find with one press off a button, for long range alignment
- High intensity green laser diode for maximised visibility; up to 4x better visibility vs red lasers
- Adjustable masking to prevent laser interference and laser reflection from windows
- Designed for harsh jobsite conditions, IP66 rated and withstands up to 1.5 m drops
- $\pm 5^\circ$ self levelling range for fast and accurate setup
- 300 metre working range with detector (RD300G), optimised for long distance applications
- Easy-to-read detector screen, mm/in back and front backlit display for clear visibility, whether used indoors or outdoors
- RD300G detector with integrated remote control allows the laser to be adjusted from distance
- Bump alert with adjustable sensitivity to notify user when laser has been moved or bumped
- 32+ hours of run time with M18 B5 battery pack
- Accuracy at ± 1.6 mm@30 m for high precision on job site
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality. The reporting function delivers a complete tool activity and accuracy protocol



REDLITHIUM™



Laser projection	1x 360°
Max. run time with M18 B5 battery (h)	32
Accuracy at 30 m distance (+/- mm)	1.6
Standard equipment	1x RD300G, detector clamp
Weight with battery pack (EPTA) (kg)	4.1 (M18 B5)
Kit included	1 x M18 B5 Battery pack, M12-18 C Charger, Kitbox
Article Number	4933493194