

Safety transformer, 40VA Primary 230 V AC, 50Hz, secondary 2x12 V/24 V AC With PTC fuse, 5 MW++



Model	
product brand name	SENTRON
product designation	Safety transformer
design of the transformer	Safety transformer
General technical data	
supplied active power / maximum	40 W
Voltage	
input voltage	230 V
output voltage	
• _1 / rated value	12 V
• _2 / rated value	24 V
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	8 W
Current	
output current	
• maximum	3.3 A

- _1 / rated value 3.3 A
- _2 / rated value 1.6 A

Suitability

suitability for integration	
<ul style="list-style-type: none"> • surface-mounted installation 	No
<ul style="list-style-type: none"> • flush mounting 	No

Product details

product component / switch	No
----------------------------	----

Product function

product function / thermal protection	Yes
---------------------------------------	-----

Inputs Outputs

property of the output / short-circuit proof	Yes
--	-----

Mechanical Design

height	64 mm
width	90 mm
length	90 mm
number of width units	5
mounting type / side-by-side mounting	Yes

Certificates

Declaration of Conformity

other

[Confirmation](#)



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AC3740-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AC3740-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4AC3740-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

