



ASP-AS-C33-JT-F

Fine Cut Pole Pruning Saw 330 mm








PRODUCT DETAILS

- Product is suitable for the applications; pruning, trimming and gardening,
- Precision ground, razor sharp JT teething provides smooth cutting and perfect result
- Strong 330 mm blade with 7,0 TPI (fine teething) for smaller branches and fine cut
- Sheath in impact-resistant plastic with quick locking and thumb grip release and belt loop
- Easier cutting of branches at height when attached to the section pole or short telescopic pole
- Reduced friction and concentrated cutting energy from the taper ground blade teething
- Hook at tip of blade to prevent slipping out of kerf
- Bark breaking blade at joint of the blade and adaptor
- The tooth tip hardened curved blade is flexible, yet stable and long lasting
- Connection adaptor for the ASP-1850 pole system, length: C33, 330 mm



PRODUCT ATTRIBUTES

Product					
ASP-AS-C33-JT-F	330 mm	13 in	7	268 g	9.5 oz

Follow the Fish!

