

Slotted Head Cap Screws

Features

- No burrs and sharp edges
- Screw material: class 4.8 carbon steel
- Trivalent blue zinc 3.8 µm min. finish
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN 84 standard

Length	L
3	2.8~3.2
4	3.76~4.24
5	4.76~5.24
6	5.76~6.24
8	7.71~8.29
10	9.71~10.29
12	11.65~12.35
14	13.65~14.35
16	15.65~16.35
20	19.58~20.42
25	24.58~25.42
30	29.58~30.42
35	34.5~35.5
40	39.5~40.5
45	44.5~45.5
50	49.5~50.5
55	54.05~55.95
60	59.05~60.95

Thread (6g)	L	PART NO.
M2x0.4	12	RND 610-00467
	16	RND 610-00468
	20	RND 610-00469
	30	RND 610-00470
M2.5x0.45	12	RND 610-00471
M3x0.5	8	RND 610-00474
	40	RND 610-00472
	60	RND 610-00473
M4x0.7	4	RND 610-00477
	16	RND 610-00475
	20	RND 610-00476
	40	RND 610-00478
M5x0.8	60	RND 610-00479
	8	RND 610-00482
	40	RND 610-00480
	50	RND 610-00481

Thread (6g)	D Head Diameter	H Head Height	N	T (Min)
M1x0.25	1.86~2.00	0.56~0.70	0.31~0.45	0.25
M1.2x0.25	2.16~2.30	0.66~0.80	0.36~0.50	0.30
M1.4x0.3	2.46~2.60	0.76~0.90	0.36~0.50	0.40
M1.6x0.35	2.86~3.00	0.86~1.00	0.46~0.60	0.45
M2x0.4	3.62~3.80	1.16~1.30	0.56~0.70	0.60
M2.5x0.45	4.32~4.50	1.46~1.60	0.66~0.80	0.70
M3x0.5	5.32~5.50	1.86~2.00	0.86~1.00	0.85
M3.5x0.6	5.82~6.00	2.26~2.40	1.06~1.20	1.00
M4x0.7	6.78~7.00	2.46~2.60	1.26~1.51	1.10
M5x0.8	8.28~8.50	3.12~3.30	1.26~1.51	1.30
M6x1.0	9.78~10.00	3.60~3.90	1.66~1.91	1.60
M8x1.25	12.73~13.00	4.70~5.00	2.06~2.31	2.00
M10x1.5	15.73~16.00	5.70~6.00	2.56~2.81	2.40

