



**Part Number :** [152660165](#)

**Product Description :** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 16 Circuits

**Series Number :** 15266

**Status :** Active

**Product Category :** Flat-Flexible Cable (FFC)



---

## Documents & Resources

### Drawings

[152660165\\_sd.pdf](#)

### Specifications

[PS-15266-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant   |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Not Contained per D(2024)7663-DC (21 Jan 2025)   |
| EU RoHS            | Compliant per EU 2015/863  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | Flat-Flexible Cable (FFC)  |
| Series       | 15266  |
| Description  | 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 16 Circuits |
| Comments     | Contacts on the same side, Type A  |
| Product Name | Premo-Flex FFC Jumper  |
| UPC          | 884982430686   |

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A   |
| Voltage - Maximum             | 60V AC |

### Physical

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 76.00mm         |
| Circuits (Loaded)             | 16              |
| Contact Layout Type           | A (same side)   |
| Design Feature                | Flexible        |
| Material - Plating Mating     | Tin             |
| Net Weight                    | 0.410/g         |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 0.50mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Termination Style             | FFC Connector   |
| Wire/Cable Type               | Flat Flex Cable |
| Wire Size (AWG)               | N/A             |

---

## Mates With / Use With

### Mates with Part(s)

| Description  | Part Number                      |
|--|----------------------------------|
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 16 Circuits, Tin-Bismuth Plating  | <a href="#"><u>525591672</u></a> |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 16 Circuits, Tin-Bismuth Plating  | <a href="#"><u>525591670</u></a> |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 16 Circuits, Tin-Bismuth                                  | <a href="#"><u>527451696</u></a> |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 16 Circuits, Tin-Bismuth Plating                       | <a href="#"><u>527461670</u></a> |
| 0.50mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Standard Footprint, Tin Bismuth Plating, Short Terminal Type, Black, 16 Circuits | <a href="#"><u>781191610</u></a> |
| 0.50mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Reverse Footprint, Tin Bismuth Plating, Long Terminal Type, Black, 16 Circuits   | <a href="#"><u>781271610</u></a> |