

## Features

- *Clear Top Sliding Fascia Panel offers an organized and secure storage for keys during lockout procedures.*
- **Tamper-Proof Central Lock Point** – Once locked with one padlock, the box contents are secured from unauthorized access.
- **Ample Key Storage** – Equipped with 16 internal key hangers for efficient and organized key management.
- **Multiple Padlock Participation** – Supports up to 29 padlocks, enabling group participation in lockout procedures.
- **Sturdy & Secure** – Built for durability and safety in demanding industrial environments.

## RS PRO 29 Group Lock Box - Top Sliding Fascia

RS Stock No.: 0694391



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Group Lock Box Top Sliding Fascia Panel offers an organized and secure storage for keys during lockout procedures.*
- *Made of high-quality ABS.*
- *Features a clear top sliding cover for easy access.*
- *Once a single padlock is placed on the central lock point, the inner contents of the box are protected and cannot be tampered with.*
- *The box has 16 internal hangers specifically designed for holding keys, providing easy organisation.*
- *There are 29 holes provided for installing lockout padlocks (sold separately), allowing multiple workers to participate in a lockout procedure.*
- *The group lock box is available with a clear tamper-proof top cover.*
- *The transparent cover enables quick identification of the keys stored inside, enhancing efficiency during lockout procedures.*
- *The box includes two rear mounting holes and a top slot in the cover for conveniently dropping in additional keys during an ongoing lockout procedure (mounting hardware included).*

## General Specifications

<b>Type</b>	Group Lock Box
<b>Material</b>	ABS
<b>Colour</b>	Yellow
<b>Padlock holes</b>	29
<b>Package</b>	BOPP + Box

## Mechanical Specifications

<b>Dimensions</b>	280mm x 330mm x 87mm
<b>Height</b>	280mm
<b>Width</b>	330mm
<b>Depth</b>	87mm
<b>Weight</b>	1.1 Kgs

## Operation Environment Specifications

<b>Withstand temperature</b>	-20 °C to 80 °C (-4 °F to 176 °F)
------------------------------	-----------------------------------