

# MARQUARDT

## SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

		ON/OFF switch (DPST)															
		1805.6102	1805.6108	1805.7104	1805.7109	1805.7110	1805.7112	1805.7118	1802.1120	1802.1121	1802.1123	1802.1136	1802.2112	1802.2504	1802.3311	1802.6123	1802.1101
Voltage lamp in V		230	230	230	230	230	110 - 230	110 - 230									
Actuator color / printing																	
Housing color		black							black								
12 (4) A 250 V AC 1E4							•	•	•	•	•	•	•	•	•	•	•
10 (4) A 250 V AC 1E4		•	•	•	•	•											•
8 (8) A 250 V AC 5E4							•	•	•	•	•	•	•	•	•	•	•
6 (4) A 250 V AC 5E4		•	•	•	•	•											•
6 (2) A 250 V AC 1E4																	
4 (3) A 250 V AC 6E3																	
4 (2) A 250 V AC 1E4																	
30 mA 12 V 5E4																	
30 mA 12 V DC 5E4																	
15 A 250 V AC 1 1/2 HP							•	•	•	•	•	•	•	•	•	•	•
15 A 125 V AC 3/4 HP							•	•	•	•	•	•	•	•	•	•	•
10 A 250 V AC 1/2 HP																	
10 A 125 V AC 1/3 HP																	
6 A 250 V AC 1/2 HP		•	•	•	•	•											•
6 A 125 V AC 1/4 HP																	•
6 A 125 - 250 V AC 1/8 HP																	
6 A 125 V AC 1/10 HP																	
4 A 250 V AC 1/10 HP																	
Connection type																	
Connection description				4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8		4.3 long	4.8 75° angled MS		4.8
Inrush current in A (capacitive)		50	50	50	50	50	70	70	70	70	70	70	70	70	70	70	70
Contact distance in mm		≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material		Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag
EN 60335 cap. 30 conform *G*							•										
Miscellaneous		installation depth 17.5	installation depth 17.5	installation depth 19.5	installation depth 19.5	installation depth 19.5	installation depth 20.5 ignition voltage < 100 V	installation depth 20.5 ignition voltage < 100 V						installation depth 16.2	shortened gate		
Stock version		•	•	•	•	•	•	•		•	•					•	•