



ENGLISH

Datasheet

Stock No: 429-694

RS Pro Grommet Strip PE 25m 1.6 → 2mm dia.



Product Details

Grommet Strips

Ideal for covering potentially dangerous edges of holes and cut outs. Flexible, extruded polythene strip with tapered continuous side walls ensuring a good grip of panels between 1 and 3.4mm thick. Minimum bend radius, 4, 5 and 6mm, minimum hole diameters 22, 25 and 30mm respectively.

Dimensions (mm)						
Max. Chassis / Panel Thickness	A	B	C	D	E	Stock no.
1.2 - 1.6	1.15 - 1.55	2.0 - 2.7	0.65 - 1.15	0.65 - 1.15	0.8 - 1.0	429-684
1.6 - 2.0	2.05 - 2.45	2.45 - 3.15	0.75 - 1.25	0.75 - 1.25	1.15 - 1.4	429-694
2.4 - 3.2	3.35 - 3.6	2.85 - 3.55	0.75 - 1.25	1.4 - 0.9	2.05 - 2.3	429-690

Specifications:

Grommet Type	Grommet Strip
Minimum Cable Diameter	1.6mm
Maximum Cable Diameter	2mm
Material	PE
Colour	Clear
Grommet Strip Length	25m