

Metal drill bits HSS PointTeQ, with hex shank

PRODUCT PROPERTIES			ORDERING INFORMATION					Part number
Diameter (D) mm	Working length mm	Total length mm	Packaging type	Pack quantity	Minimum order quantity		Barcode	
7.5	69	109	PC1d	1	5		6949509231475	2 608 577 532
8	75	117	PC1d	1	5		6949509231482	2 608 577 533
8.5	75	117	PC1d	1	5		6949509231499	2 608 577 534
9	81	125	PC1d	1	5		6949509231505	2 608 577 535
9.5	81	125	PC1d	1	5		6949509231512	2 608 577 536
10	87	133	PC1d	1	5		6949509231529	2 608 577 537
11	94	142	PC1d	1	5		6949509231536	2 608 577 538
12	101	151	PC1d	1	5		6949509231543	2 608 577 539

Pack of 5

8	75	117	P1h	5	1		6949509231628	2 608 577 547
10	87	133	P1h	5	1		6949509231635	2 608 577 548
12	101	151	P1h	5	1		6949509231642	2 608 577 549

Pack of 10

2	24	60	P1h	10	1		6949509231550	2 608 577 540
3	33	72	P1h	10	1		6949509231567	2 608 577 541
3.5	39	79	P1h	10	1		6949509231574	2 608 577 542
4	43	83	P1h	10	1		6949509231581	2 608 577 543
4.2	43	83	P1h	10	1		6949509231598	2 608 577 544
5	52	91	P1h	10	1		6949509231604	2 608 577 545
6	57	98	P1h	10	1		6949509231611	2 608 577 546