

FEATURES

- **304 Stainless Steel**
Material: Provides excellent corrosion resistance and durability.
- **Concealed Hinge Design:**
Offers a clean and professional look, hiding the hinge from view.
- **Removable Pin:** Allows for easy installation and maintenance.
- **Bolt-On/Rivet Fixing**
Method: Ensures secure attachment and stability.
- **6.5 mm Fixing Hole Size:**
Compatible with standard bolt sizes for easy installation.
- **24.5 mm Width and Thickness:** Provides a robust and sturdy structure.

RS PRO 80 mm Concealed Hinge, 304 Stainless Steel

RS Stock No: 335-153



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

The RS PRO 80 mm concealed hinge is designed for applications requiring a discreet and robust hinge solution. Made from high-quality 304 stainless steel, this hinge is ideal for environments where corrosion resistance and durability are paramount. Its concealed design ensures a clean and professional appearance, making it suitable for a variety of industrial and commercial uses.

General Specifications

Fixing Hole Size	6.5 mm
Fixing Method	Bolt-On/Rivet
Hinge Type	Concealed
Holes per Leaf	2
Pin Style	Removable Pin
Product Type	Concealed Hinge

Mechanical Specifications

Length	80 mm
Material	304 Stainless Steel
Thickness	24.5 mm
Width	24.5 mm

Approvals

Standards/Approvals	REACH, RoHS
---------------------	-------------