
Automatic bundling up to Ø 20 mm

Cable ties for Autotool 2000 systems

The inside-serrated cable ties are designed for use specifically in the automatic cable tying systems. The Autotool 2000 CPK is ideally suited for handling high volumes applications in wire harness facilities, automotive and industrial companies as wells as the packaging sector.

Features and benefits


- Heat stabilised cable ties (PA66HS) in all colours for temperatures up to +125 $^{\circ}\text{C}$
- Available in bandoleers of 50 cable ties or reels of 3,500 cable ties
- Repetitive tension on the bundles
- · Easily recyclable



Cable ties for Autotool 2000 systems.

MATERIAL	Polyamide 6.6, heat stabilised (PA66HS)	Polyamide 6.6, heat and UV-resistant (PA66HSW)	Polyamide 4.6 (PA46)
Operating Temperature	-40 °C to +105 °C, (+145 °C, 500 h)	-40 °C to +130 °C, (+150 °C, 5000 h; +195 °C, 500 h)	
Flammability	UL 94 V2		








Please find the corresponding Bundling Clips on page 170.

Bandoleer	T18RA
Danadicci	110101

ТҮРЕ	Bundle Ø max.	N	Colour	Material	Pack Cont.	Article-No.
T18RA50	20.0	80	Black (BK)	PA66HSW	2,000 pcs.	120-40020
T18RA3500	20.0	80	Black (BK)	PA66HSW	3,500 pcs.	120-50010
	20.0	80	Natural (NA)	PA46	3,500 pcs.	120-46009
T18RA50	20.0	80	Natural (NA)	PA66HS	2,000 pcs.	120-40019
T18RA3500	20.0	80	Natural (NA)	PA66HS	3,500 pcs.	120-50009

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

Halogen-free according to the interdictions of the GADSL list and compulsory registration of the SVHC list.





For product specific approvals and specifications please refer to the Appendix.