

## Trousers OPTIMAX CP - 2029 -



### REFERENCES AND SIZES

Sizes: 36 to 64 - 84cm inside leg

Grey : 2029.2351.926

Azure blue : 2029.2351.954

Gaulois blue : 2029.2351.956

Alpine green : 2029.2351.213

Green : 2029.2351.921

Navy : 2029.2351.958

### DESCRIPTION



PLASTIC  
ACCESSORIES



ABRASION  
RESISTANCE



EN 15797



MANY POCKETS



ELASTIC  
WAISTBAND



PREFORMED  
ELEMENTS

- ▶ Sewn waistband fastened by a single button in black polyester; elasticated at the sides; 5 belt loops, including 1 at the left front in herringbone tape. A loop in black tape to hang keys, sewn into the waistband at the right front.
- ▶ Italian pockets with angled lower corner.
- ▶ 2 thigh patch pockets with a front side gusset, flap with hook and loop fastening.
- ▶ Right thigh pocket has a ruler pocket, accessible via an opening at the top of the back flap.
- ▶ Knees preshaped with darts.
- ▶ 2 topstitched back darts.
- ▶ 1 left back patch pocket with a hanging bottom, flap with hook and loop fastening.
- ▶ 1 right back telephone pocket with side gussets, flap with hook and loop fastening.
- ▶ For the grey, Gaulois blue and navy: spiral zip fastening with a plastic slider.

### FABRIC

Main fabric: Twill 2/2, 60% cotton, 40% polyester, 315g/m<sup>2</sup>

### MARKING

'M' embroidered in black below the left Italian pocket

### CARE

