

C701 - Combat Trousers

Collection: General Workwear

Range: Workwear

Shell Fabric: Kingsmill Polycotton: 65% Polyester, 35% Cotton, 245g

Outer Carton: 36

Product information

This garment portrays all the original styling of the modern-day work trouser. Constructed from our rugged, pre-shrunk Kingsmill fabric, the Combat Trousers are built to take on the toughest of jobs. Multiple utility pockets are featured with Hook and Loop flaps for added security.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.



Features

- Durable polycotton fabric for high performance and maximum wearer comfort
- 6 pockets for ample storage
- 2 Back pockets
- 2 Cargo pockets
- Hook and loop closure for easy access
- Reinforced seams for extra durability and strength
- 2 Side pockets
- 40+ UPF rated fabric to block 98% of UV rays
- Bartacked at all stress points
- An improvement has been made to the current fit of the product
- Anti-scratch design with no exposed metal parts

C701 - Combat Trousers
Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
C701BKR26	Black	43.0	28.0	52.0	0.4800	0.0626	5036108243655	25036108731996
C701BKR28	Black	43.0	28.0	52.0	0.2400	0.0626	5036108039029	25036108613926
C701BKR30	Black	43.0	28.0	52.0	0.4480	0.0626	5036108039036	25036108613933
C701BKR32	Black	43.0	28.0	52.0	0.4520	0.0626	5036108039043	25036108613940
C701BKR33	Black	43.0	28.0	52.0	0.4610	0.0626	5036108384945	25036108869507
C701BKR34	Black	43.0	28.0	52.0	0.4800	0.0626	5036108039050	25036108613957
C701BKR36	Black	43.0	28.0	52.0	0.4980	0.0626	5036108039067	25036108613964
C701BKR38	Black	43.0	28.0	52.0	0.5040	0.0626	5036108039074	25036108613971
C701BKR40	Black	43.0	28.0	52.0	0.5120	0.0626	5036108039081	25036108613988
C701BKR41	Black	43.0	28.0	52.0	0.5050	0.0626	5036108384952	25036108869514
C701BKR42	Black	43.0	28.0	52.0	0.5220	0.0626	5036108039098	25036108613995
C701BKR44	Black	43.0	28.0	52.0	0.5510	0.0626	5036108039104	25036108614008
C701BKR46	Black	43.0	28.0	52.0	0.5460	0.0626	5036108039111	25036108614015
C701BKR48	Black	43.0	28.0	52.0	0.6000	0.0626	5036108039128	25036108614022
C701BKR50	Black	43.0	28.0	52.0	0.6200	0.0626	5036108368570	25036108857603