










Projection		Scale	Free	DATE	03-31-2025
Drawing No.	LVQ20-Z07R-5				

LVQ20-Z07R-5

Air Operated Flare, Integral Fitting Type Hyper Fitting

3D View

To activate the interactive 3D view, you must trust this document (see hint on the top) in Adobe Acrobat and click on the question mark.



LVQ20-Z07R-5

Air Operated Flare, Integral Fitting Type Hyper Fitting

Technical Data

CLASS (Body class)	2
VALVE (Valve type)	(0) N.C.
FITTING (Fitting type)	(Z) LQ3 integrated fitting
SIZE (Applicable tubing size)	(07) Inch: 1/4 x 5/32
PILOT (Pilot port type)	(R) Threaded, Rc1/8
DIRECTION (Pilot port direction / °)	(-) 0
OPTION1 (Option 1)	(5) High back pressure (0.42 MPa)
OPTION2 (Option 2)	(-) None
A ()	25.5
B ()	46
C ()	31.5
D ()	58
E ()	33.6
F ()	56.5
G ()	12.0
HV ()	70
HS ()	77
J ()	21.8
K ()	37.0
L ()	5
M ()	7
N ()	15
P ()	53.5
Q ()	21.0
R ()	25.3
W ()	64.0
S ()	56
T ()	34.3
U ()	10.6
V ()	7