

## DCE079D1G-QW

18V XR Green Rotary Laser - 1 X 2Ah



5035048657966



### Product Description :

Self Levelling 360° Rotary Laser projects bright beam either horizontally or vertically. Durable design with IP67 rated water and debris resistance makes it ideal for outdoor applications. Manual RPM Control. Easy to use with full onboard and remote control panel. Long range visibility.

### Product Features and Benefits :

- Rated to IP67 for maximum protection against water and dust ingress
- Powered by 18V 2Ah XR or XR FLEXVOLT battery
- Green beam technology delivers outstanding visibility in challenging lighting conditions, both inside and outdoors – up to four times more visible to the human eye than red beam lasers
- Full Automatic Horizontal and Vertical Self LEVELING laser +/-5°
- Plumb Dot Up and Down
- Single Slope Mode allows user to set grade
- +/- 3mm accuracy per 30m
- +/- 15 / 45 / 90° Scan Mode
- Manual RPM Control (rotation per minute): 150, 300, 600, 1200
- Integrated 5/8" thread for tripod mounting

### Technical specifications :

- Visible Working Distance - Diameter [Metric] : 60 m
- Working Distance with Detector - Diameter [Metric] : 600 m
- Working Distance with Detector [Metric] : 600 m
- Visible Working Distance [Metric] : 60 m

### Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

### Included items :

- Briefcase TSTAK (x1)
- XR 18V/2Ah Battery (x1)
- Charger (x1)
- Target (x1)
- Laser Detection Glasses (x1)
- Remote Control (x1)
- Detector (x1)

