

**ZM17** **Precision locknut**

Precision locknut ZM, accessory ZM..

Technical information**Main Dimensions & Performance Data**

d	M17X1	Thread
D	28 mm	Outside diameter
h	10 mm	Height
M _A	3 Nm	Mounting torque set screw
F _{aB}	57,000 N	Breaking load, axial
M _L	30 Nm	Breakawag
M _{AL}	15 Nm	Mounting torque reference
M _M	0.401 kg*cm ²	Mass moment of inertia
≈m	27.26 g	Weight

Dimensions

d ₁	23 mm	Plant diameter outside
t	2 mm	Hight retaining slot
b	4 mm	Width retaining slot
c	5 mm	Distance bore
m	M5	Threaded - threaded pin