



ENGLISH

Datasheet

RS Pro Bright Zinc Plated Steel Nylon Insert Locking Nut, M12

RS Stock No: **530-416**



Product Details

RS Pro nylon insert locking nut made of bright zinc plated steel offers corrosion resistance. This nut is self locking due to glass filled nylon insert and features M12 metric internal threading to couple with threaded rod. The nut is designed to remain secure despite conditions of severe vibration.

Features and Benefits

- Grade 8 steel, bright zinc plated
- M12 metric threading
- Self-locking due to glass filled nylon insert
- Remain secure despite conditions of severe vibration

**Specifications:**

Finish	Bright Zinc Plated
Material	Steel
Thread Size	M12
Type	Nylon Insert
Grade	8
Specification	DIN 982
Thickness	14.2 to 14.9 mm
Thread Pitch	1.75
Width Across Corners	20.03 mm
Width Across Flats	17.73 to 18 mm
Wrenching Height	8.3 mm