



PRODUCT-DETAILS

SPL16/25M

16MM GS-PVC COAT CONDUIT 25M - BL



General Information

Extended Product Type:	SPL16/25M
Product ID:	7TCA296030R0078
EAN:	5020963000560
Catalog Description:	16MM GS-PVC COAT CONDUIT 25M - BL
Long Description:	Liquid Tight, Oil Resistant, Medium Flexibility Conduit, Nominal Conduit Size 16mm, Outside Diameter 17.8mm, Inside Diameter 12.5mm, Static Bend Radius 50mm, Reel Length 25 Meters, PVC Covering with Galvanised Steel Core, Black
Display Name:	SPL16/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Liquid Tight - Indoors / Outdoors, Marine, Buildings

Ordering

EAN:	5020963000560
-------------	---------------

UPC: 786210239392

Dimensions

Outside Diameter: 17.8 mm

Technical

Number of Batteries: 0

Color: Black

Material: Galvanized Steel Core with PVC Covering

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963000560

Package Level 1 Height: 6 in
152 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

