

Part Number:0874370263

Status:Active

Overview:Pico-SPOX Wire-to-Board Connector System

Description:1.50mm Pitch, Pico-SPOX PCB Header, Single Row, Vertical, Surface Mount, Tin (Sn) Plating, Friction Lock, 2 Circuits, Tape and Reel, with Cap, Black

Documents:

3Dモデル

3D モデル (PDF)

図面 (PDF)

製品仕様書 PS-87437-001-001 (PDF)

圧着仕様書 874370000-AS-000 (PDF)

梱包仕様書 SPK-87437-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
一般用途概要製品名UPC	
Signal, 電線対基板	
Pico-SPOX Wire-to-Board Connector System	
Pico-SPOX	
822350757454	
機械的性能/材質	
分離型	無
極数 (実装)	2
極数 (最大)	2
色 - 樹脂部	黒色
耐久挿抜回数	10
活線挿抜対応	無
難燃性	94V-0
Glow-Wire Capable	無
嵌合ガイド	無
嵌合キー	無
嵌合ロック	Yes
材質 - 金属部	黄銅
材質 - 嵌合部メッキ	錫
材質 - ターミナルメッキ	錫
材質 - 樹脂部	ナイロン
Net Weight	0.158/g
列数	1
実装形態	ストレート
位置決め	無
基板保持	無
梱包形態	エンボステーピング
ピッチ - 嵌合部 (インチ)	1.50mm
嵌合部メッキ厚	2.540µm
ターミナルメッキ厚	2.540µm
嵌合極性	Yes
基板極性	無
自動実装対応	自動実装用キャップ
シュラウド	フルシールド
縦列スタック (エンド・ツー・エンド)	無
使用温度範囲	-55° to +105° C
実装スタイル	SMT (表面実装)
電氣的性能	
最大定格電流	2.5A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
ED/71/2019 (16 July	
2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit	
Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

87437 Series

Mates With

Pico-SPOX Wire-to-Board Housing 87439

最大定格電圧

250V AC (RMS)/DC

参考情報

図面・仕様書情報

圧着仕様書

874370000-AS-000

梱包仕様書

SPK-87437-001-001

製品仕様書

PS-87437-001-001

製品図面

874370231-SD-000, SD-87437-001-001

This document was generated on 01/20/2020
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION