

ABH 18

Cordless rotary hammer drill
Order number:: 7 140 01 64 00 0

FEIN SELECT⁺



Extremely compact and powerful cordless rotary hammer drill with an impact energy of 2 J for drilling up to 20 mm in concrete.

- Rapid work progress thanks to brushless motor with high impact energy.
- Fatigue-free working thanks to compact design and few vibrations.
- Protection for the user and tool by means of safety clutch and overload protection.
- Combination hammer with three functions: hammer drilling, drilling and chiselling.
- Brushless motor with 30% higher efficiency and long service life.
- 80 holes (10 x 75 mm) with one battery charge (5 Ah).
- Producing 68 mm socket holes with drill bit in masonry.
- The optional drilling dust nozzle means that little dust is produced.
- Low-vibration working at just 12 m/s².
- FEIN SafetyCell technology. Protects the battery and tool from overload, overheating and total discharge.
- 3-year FEIN PLUS warranty including battery and charger.
- The battery charge can be read off the battery.



ABH 18

Cordless rotary hammer drill
Order number:: 7 140 01 64 00 0

Technical data

Battery voltage	18 V
Motor	brushless
Speed, no load	0 - 1 200 rpm
Impacts	0 - 4 400 rpm
Impact energy	2,0 J
Tool Holder	SDS-plus
Hole diameter, concrete	20 mm
Hole diameter, masonry	68 mm
Capacity in steel Ø	13 mm
Capacity in wood Ø	22 mm
Weight without battery	2,30 kg
Cordless	X

Included in price::

- 1 handle
- 1 depth stop
- 1 plastic carrying case