

FH202 AC-25/0,03



FH202 AC-25/0,03 Residual Current Circuit Breaker



General Information

Extended Product Type	FH202 AC-25/0,03
Product ID	2CSF202002R1250
EAN	8012542891802
Catalog Description	FH202 AC-25/0,03 Residual Current Circuit Breaker
Long Description	The RCCBs FH200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous AC and A types is particularly suitable for installation in domestic applications.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Popular Downloads

Data Sheet, Technical Information	2CSC400030D0202
Instructions and Manuals	Printed on product

Dimensions

Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.200 kg

Technical

Standards	IEC/EN 61008
Operating Characteristic	Instantaneous
Type of Residual Current	AC type
Rated Residual Current	30 mA
Rated Current (I_n)	25 A
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 1 W

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5603
Environmental Information	Refer to RoHS
Instructions and Manuals	Printed on product
RoHS Information	2CSC423001K2702

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.041 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.225 kg
Package Level 1 EAN	8012542891802

Classifications

Object Classification Code	Q
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

