

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936014369](#)

**Status:** **Active**

**Overview:**

**Description:** GWconnect STD - Standard, Double Lever Bulkhead Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 32B «77x62», Grey

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
Series [93601](#)  
Component Size 32B «77X62»  
Component Type Double Lever Bulkhead Housing  
IP Rating IP66  
Overview hdc\_heavy\_duty\_connectors  
Product Category Heavy Duty Connectors  
Product Name GWconnect  
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
Type STD  
UPC 887191894652

**Physical**

Housing Coating Polyester Powder  
Housing Color Grey RAL 7037  
Lock to Mating Part Yes  
Material - Gasket NBR  
Material - Housing Die-cast Aluminum  
Material - Lever Galvanized Steel  
Mounting Style Bulkhead  
Net Weight 236.000/g  
Number of Levers 2  
Packaging Type Bag  
Thread Size N/A  
Thread Type N/A

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7832.6415.0



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

Green Image

Not Relevant

Not Contained

CER\_4000400780\_00\_000.pdf

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 32B «77x62» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts