

FEATURES

- Titanium Nitride Coated (TiN)
- Longer shaft length
- Right angle cutting tip
- 118° cutting angle
- Available in sizes from 0.25mm – 20mm

RS PRO HSS Twist Drill Bit, 9mm x 125mm

RS Stock No.: 214-048



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

High speed titanium nitride coated jobber drill bits, suitable for a multitude of jobs and materials feature a longer shaft compared to other standard drill bits and can be used in both hand and machine drills. Suitable for drilling metal, wood and plastic along with a range of other materials, jobber drill bits feature right hand cutting tip with 118° cutting angle.

General Specifications

Drill Bit Type	Twist Drill Bit
Type	Twist
Material	HSS
Surface	Tin-coated
Drilling Application	Metals, woods, plastics

Mechanical Specifications

Overall Length	125mm
Point Angle	118°
Diameter	9mm
Flute Length	81mm

Approvals

Compliance/Certifications	DIN 338; BS 328-ISO 235/1
----------------------------------	---------------------------

