



## Main

Range	TeSys
Device short name	LU9G
Product or component type	Profibus DP power supply module
Product compatibility	LULC07

## Complementary

[Us] rated supply voltage	24 V DC
Maximum current I <sub>rms</sub>	<= 1.5 A
Width	45 mm
Height	170 mm
Depth	65 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1036 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------