

MATERIAL & FINISH

Housing: Liquid crystal polymer, UL 94-0

Contact: Phosphor bronze

Contact Plating: Tin plated

Gold plated

Current Rating: 1 Amp.

Withstanding Voltage: AC 250V for 1 minute.

Insulation Resistance: 1000 M Ω Minute at DC 250V

Termination Resistance: 20 m Ω max. at DC 100 mA.

Operation Temperature: -55°C to + 105°C