



**Part Number :** [1451320700](#)  
**Product Description :** Micro-Fit TPA-to-Micro-Fit TPA  
Off-the-Shelf (OTS) Cable Assembly, Single Row,  
75.00mm Length, 7 Circuits, Black  
**Series Number :** 145132  
**Status :** Active  
**Product Category :** Power and Signal Cable  
Assemblies



## Documents & Resources

### Drawings

[1451320700 sd.pdf](#)

### 3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	145132
Description	Micro-Fit TPA-to-Micro-Fit TPA Off-the-Shelf (OTS) Cable Assembly, Single Row, 75.00mm Length, 7 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit TPA Both Ends
Product Name	Micro-Fit TPA
Type	Discrete Wire Assembly
UPC	191130115754

### Electrical

Current - Maximum per Contact	8.5A
Voltage - Maximum	300V AC/DC

### Physical

Cable Length	75.00mm
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black
Gender	Female-Female

Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	6.970/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Single Row Plug Housings	<u><a href="#">43640</a></u>
Micro-Fit TPA Single Row Plug Housings	<u><a href="#">200875</a></u>
Micro-Fit 3.0 Single Row Headers	<u><a href="#">43650</a></u>