

## 2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p

Product ID: VS221HDQ



Save time and hassle by automatically switching between your HDMI audio/video sources, using the VS221HDQ 2-Port HDMI Auto Switcher. This easy-to-use HDMI switch ensures seamless transition while switching video sources, with EDID copy maintaining your video resolution.

### Seamless Signal Selection

Ensure seamless transition while switching video sources, with EDID copy maintaining native resolution with support for 1080p. Video connection emulation ensures the settings on any connected computers are not disrupted while switching to a different video source.

### Effortless Control

Save time by connecting two HDMI video source devices to your HDMI display instead of manually connecting individual cables. Mounting hardware is also included for a tidy, professional installation.

## Versatile Switching Options

Enjoy hassle-free operation with three different switching modes:

**Automatic port selection:** Enables your most recently activated video source to be displayed automatically.

**Priority port selection:** Prioritizes input number two above input number one. If the video source connected to input number two is activated that source will be displayed.

**Manual port selection:** Enables you to manually select your HDMI source with easy-to-use front panel buttons.

This product is TAA compliant and backed by a Startech.com 2 warranty with lifetime technical support

### Certifications, Reports and Compatibility



### Applications

- Automatically switch between your Blu-ray player, set top box, or gaming console in a home theatre environment
- Connect and switch between two video sources on a test bench, for troubleshooting computers
- Switch between different video sources on your digital signage display in hospitals, shopping centers, or schools

### Features

- Auto switching
- Priority switching
- Built-in manual control console
- EDID emulation
- Video connection emulation
- Support for video resolution up to 1080p
- Mounting hardware included

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	AV Input	HDMI
	AV Output	HDMI
	Cabling	HDMI
	Ports	2
	Rack-Mountable	Yes
<b>Performance</b>	Audio Specifications	7.1 surround sound
	Max Distance	10 m / 33 ft
	Maximum Digital Resolutions	1920x1200 / 1080p
	Supported Resolutions	1920x1200 1920x1080 (1080p) 1280x720 (720p)
<b>Connector(s)</b>	Connector A	2 - HDMI (19 pin) Female
	Connector B	1 - HDMI (19 pin) Female
<b>Indicators</b>	LED Indicators	1 - Source #1 activated 1 - Source #2 activated
<b>Power</b>	Input Current	0.6 A
	Input Voltage	100 ~ 240 AC
	Output Current	1.5 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	18
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0%~80%
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Aluminum and Plastic
	Product Height	0.8 in [20 mm]
	Product Length	6.1 in [156 mm]
	Product Weight	10.2 oz [290 g]

	Product Width	2.6 in [65 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	30.1 oz [853 g]
<b>What's in the Box</b>	Included in Package	1 - HDMI auto switch 1 - universal power adapter (NA, EU, UK, AU) 1 - remote control 1 - foot pad set 1 - mounting kit 1 - instruction Manual

Product appearance and specifications are subject to change without notice.