



Main

| | |
|-----------------------------|-------------|
| Range of product | OptiLine 45 |
| Cabling installation system | Post |
| Product type | Post |
| Type of post | One-sided |
| Pole/post surface finish | Anodized |

Complementary

| | |
|---------------------------|---------------------------------|
| Colour | Natural |
| Fixing mode | Screw-fixed |
| Front opening size | 45 mm |
| Material | Aluminium anodized |
| Quantity package 1 / unit | Set of 1 |
| Height | 700 mm |
| Width | 68 mm |
| Market segment | Small commercial Residential |

Environment

| | |
|-------------------------|--|
| Standards | 73/23/EEC 93/68/EEC EN 50085-1:2005 EN-AW-6063 NF C 68-102 |
| Operating temperature | -25...60 °C |
| IP degree of protection | IP30 |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |