

# Rittal – The System.

Faster – better – everywhere.

## ► Baying enclosure system VX25 Distribution enclosures – VX 9666.926

Date : Jun 19, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Baying enclosure system VX25 Distribution enclosures – VX 9666.926

created: 19.06.2019 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Material:</b>	Sheet steel
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 55
<b>Protection category NEMA:</b>	NEMA 12
<b>Basis of test:</b>	IEC 61 439-1/-2
<b>Supply includes:</b>	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Gland plates Rear panel Roof plate
<b>Note:</b>	For 600 mm wide distribution enclosures, please use basicenclosures

## Product features

<b>Dimensions:</b>	Width: 1100 mm Height: 2000 mm Depth: 600 mm
--------------------	--

<b>Number of doors:</b>	2
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	156 kg
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177929616
<b>Customs tariff number:</b>	94032080
<b>ETIM 6.0:</b>	EC000214
<b>ETIM 5.0:</b>	EC000214
<b>eCl@ss 8.0/8.1:</b>	27142409
<b>eCl@ss 7.0/7.1:</b>	27142409
<b>eCl@ss 6.0/6.1:</b>	27142409
<b>eCl@ss 5.1/5.1.4:</b>	27370302
<b>Product description:</b>	VX Distribution enclosure (ISV), WHdepth 1100x2000x600 mm, sheet steel, two-door