



## APC Replacement Battery Cartridge #48

Part Number: RBC48



### Batteries & Runtime

Battery Volt-Amp-Hour Capacity

168

Battery Type

Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting

Stand alone battery stack

Battery manufacturer

--

Expected Battery Life (years)

3 - 5

RBC™ Quantity

1

Battery blocks per string

2

### Physical

Net Weight

5.00 KG

Maximum Height

108.00 mm

Maximum Width

132.00 mm

Maximum Depth

150.00 mm

Shipping Weight

5.91 KG

Shipping Width

168.00 mm

Shipping Height

168.00 mm

Shipping Depth

224.00 mm

Units per Pallet

40.00

### Environmental

Operating Environment

0 - 40 °C

Operating Relative Humidity

0 - 95%

Operating Elevation

0-3000 meters

Storage Temperature

-15 - 45 °C

Storage Relative Humidity

0 - 95%

Storage Elevation

0-15000 meters

### Conformance

Standard Warranty

1 year repair or replace

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.