

Product data sheet

Specifications

Repacked, GT bend, Mureva Tube
GT, diameter 25mm, IP40, grey



IMT53325W



This repacked option saves 9.952 over the standard condition

Main

range of product	Mureva
Product or component type	Bend
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	359 mm ²
Diameter	External: 25 mm Internal: 21.4 mm
Colour tint	Grey (RAL 7035)

Complementary

Quantity per set	20 pieces
Ambient air temperature for operation	-5...60 °C
Material	PVC (polyvinyl chloride)
Standards	IEC 61386

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Product certifications	NF

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	19 cm
Package 1 Length	20 cm
Package 1 Weight	62 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	20 cm
Package 2 Width	19 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	30 cm
Package 2 Weight	1.25 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	120
Package 3 Height	40 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	8.022 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

10 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

90215406-b6bf-44f8-b463-8540d32a6f6b

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No