

ENTE :
BODY :


CSA

Simbolo :
Symbol :



Riconosciuto conforme alle norme : CAN/CSA C22.2 No. 14-95
In accordance to standards :

TIPO TYPE	Corrente nominale Nominal current Tensione nominale Nominal voltage	Vita elettrica a pieno Carico in AC1 (cicli) Electrical life at AC1 rated load (cycles)	Portata Motore Motor rating	Temperatura ambiente Ambient temperature	N. File
55.X2 - X3	10 A - 277 Vac	/	1/3 Hp - 110-120 Vac 3/4 Hp - 220-240 Vac	40 °C	LR 28197-44
55.X4	7 A - 277 Vac		1/8 Hp - 110-120 Vac 1/3 Hp - 220-240 Vac	55 °C	

Emissione LO Approvazione UT		Livello di revisione nr. 11	DATA REVISIONE 24.02.2003	PAGINA NR. 1/8
---------------------------------	---	-----------------------------------	------------------------------	-------------------