

27102 SIL

- Part number : 27102 SIL
- Body : Composite
- Nozzle : Composite
- Triger : Progressive
- Insert : 1/4 BSP female metal thread
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Silent nozzle
- Non scratch body
- Crush resistant
- Flow @ 6 b : 12 m³/h - 7 cfm
- Sound level : 77 db
- Nozzle lenght : 56 mm - 2.2 in
- Blowing force : 213 g
- Dynamic pressure : 0 b
- Weight : 116 g

