

B303 - Hi-Vis Sweatshirt

Collection: High Visibility Sweatshirt Range 65% Polyester 35% Cotton

Range: High Visibility

Shell Fabric: 65% Polyester, 35% Cotton

Outer Carton: 24

Product information

The B303 sweatshirt is ideal when it's too cool for a T-shirt but not cold enough for a jacket. Offering exceptional comfort, the fit is roomy and the fabric is soft to touch. Available in yellow, red and rail specification orange (RIS-3279-TOM).

High Visibility Sweatshirt Range 65% Polyester 35% Cotton

Our high visibility sweatshirts are made from a special blend of 65% polyester 35% cotton with a brushed back for extra warmth and comfort. The fabric provides breathability and flexibility combined with superior strength and durability and is manufactured to withstand the most rigorous working environments.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 3
RIS 3279 TOM Issue 2 (Orange Only)
ANSI/ISEA 107 TYPE R CLASS 3
ANSI/ISEA 107 TYPE P Class 3



Features

- Knitted fabric with brushed backing
- Ribbed cuffs for added comfort
- Ribbed hem for a comfortable fit
- Generous fit for wearer comfort
- Bio motion tape pattern to improve recognition of human shape at distance
- Reflective tape for increased visibility
- 40+ UPF rated fabric to block 98% of UV rays
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified
- UKCA marked



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

B303 - Hi-Vis Sweatshirt
Commodity Code: 6110301000

Test House
OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
Sebenhirtenstrasse 12A
1230, Austria
Contact: Marion Pfeiler
Cert No: VN605 151689.3

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
B303ORRXS	Orange	55.0	41.0	45.0	0.5100	0.1015	5036108256242	25036108745153
B303ORRS	Orange	55.0	41.0	45.0	0.5800	0.1015	5036108145256	25036108606645
B303ORRM	Orange	55.0	41.0	45.0	0.5600	0.1015	5036108145263	25036108606638
B303ORRL	Orange	55.0	41.0	45.0	0.5900	0.1015	5036108145270	25036108606621
B303ORRXL	Orange	55.0	41.0	45.0	0.6400	0.1015	5036108145287	25036108606652
B303ORRXXL	Orange	55.0	41.0	45.0	0.6380	0.1015	5036108145294	25036108606669
B303ORRXXXL	Orange	55.0	41.0	45.0	0.7000	0.1015	5036108145300	25036108606676
B303ORR4XL	Orange	55.0	41.0	45.0	0.7600	0.1015	5036108145317	25036108606614
B303ORR5XL	Orange	55.0	41.0	45.0	0.7560	0.1015	5036108202331	25036108688054