

tesa® 60299 Plastering Tape

tesa® 60299 is a specially formulated plasticized PVC tape with low unwinding force and high adhesion at low temperature with a flat film.

Having a soft modified and thick rubber adhesive coating tesa® 60299 is suitable for most rough surfaces.

The tape can withstand humidity, weak alkaline solutions, acids and many other chemicals.

Main Application

tesa® 60299 is suitable for masking during plastering, painting, gypsum, masonry and stucco work. It protects the surfaces of sensitive profiles and facings against dirt and damage through manufacturing tools and material.

It is also suitable for the sealing of bags, heavy duty wrapping and other DIY applications.

Technical Data

▪ Backing material	PVC film	▪ Elongation at break	125 %
▪ Total thickness	120 µm	▪ Tensile strength	16 N/cm
▪ Type of adhesive	natural rubber	▪ UV-resistance	2 weeks
▪ Adhesion to steel	2.4 N/cm		

Additional Information

The tape can be used for temperatures above 0°C.

For latest information on this product please visit <http://l.tesa.com/?ip=60299>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.