

### FR28 - Bizflame Work FR Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 280g

**Outer Carton:** 12



### Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Work fabric.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

### Standards

EN ISO 11612 (A1+A2, B1, C1, F1)  
EN ISO 11611 Class 2 (A1+A2)  
EN 1149 -5  
EN 17353 Type B2

### Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Two tier knee pad pockets allowing two positioning options
- Side access openings
- Sleeve pocket
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

### FR28 - Bizflame Work FR Coverall Commodity Code: 6211321000

#### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
Bracetown Business Park  
D15 YN2P, Ireland  
Cert No: 2777/13017-03/E00-00

#### Wash Care



#### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR28ORRXS	Orange	43.0	28.0	46.0	1.2390	0.0554	5036108202553	15036108688217
FR28ORRS	Orange	43.0	28.0	46.0	1.3160	0.0554	5036108186655	15036108625625
FR28ORRM	Orange	43.0	28.0	46.0	1.3860	0.0554	5036108186648	15036108625618
FR28ORRL	Orange	43.0	28.0	46.0	1.4200	0.0554	5036108186631	15036108625601
FR28ORRXL	Orange	43.0	28.0	46.0	1.4730	0.0554	5036108186662	15036108625632
FR28ORRXXL	Orange	43.0	28.0	46.0	1.4830	0.0554	5036108186679	15036108625649
FR28ORRXXXL	Orange	43.0	28.0	46.0	1.5330	0.0554	5036108186686	15036108625656
FR28ORR4XL	Orange	43.0	28.0	46.0	1.6170	0.0554	5036108228737	15036108716491