

Main

Range	New Unica
Product or component type	Telephone socket
Device application	Communication
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)
Telephone socket type	France Telecom (8 contacts)




Complementary


Socket number	1
Number of modules	2 modules
Connections - terminals	Screw terminals
Connections - terminals	Screw terminals 4 pairs cable
Fixing mode	Clip-in
Material	Thermoplastic ABS-UV stabilised: centre plate
Depth	36 mm
Width	45 mm
Height	45 mm
Embedding depth	20 mm
Net weight	0.026 kg
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP20
IK degree of protection	IK02

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins