


## FEATURES

- **Non-Dimmable:** Simplifies installation and reduces complexity in lighting systems
- **4.17 A Driver Current:** Provides consistent power output for optimal LED performance
- **Input Voltage Range 176 – 264 V AC:** Compatible with a wide range of AC power sources
- **IP67 Rated:** Offers protection against dust and water, ideal for outdoor or industrial use
- **Maximum Output Power 100W:** Supports high-power LED applications
- **Constant Voltage Operation:** Ensures stable and reliable LED illumination

## RS PRO 100W LED Driver, 24V Constant Voltage

RS Stock No: 642-779



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO 100W LED Driver is designed to provide reliable power for LED lighting systems. With a constant voltage output of 24V, it ensures stable performance for a variety of lighting applications. Its robust design and IP67 rating make it suitable for use in challenging environments.

### General Specifications

Dimming Operation	Non-Dimmable
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	4.17 A
Input Voltage	176-264 V ac
Input Voltage Type	AC
Maximum Output Power	100 W
Output Voltage	24 V

### Protection Category

IP Rating	IP67
-----------	------

### Approvals

Standards/Approvals	CE, EEN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, EN61000-4-2,3,4,5,6,8,11, EN61347-1, EN61347-2-13
---------------------	--