

## Datasheet

# RS Pro 24V, 25A Lead Acid Battery Charger, UK Plug

RS Stock No: **549-287**



## Product Details

RS Pro lead acid battery charger is a high quality range of automatic charger with 3 stage controls. The charger yields 24 V output voltage at 25 A charge current. The UK plug type charger has a charging current(s) of 2 to 25 A with many models provided in aluminium impact resistant casing and supplied with UK and EU mains leads and crocodile clip connectors. The battery charger meets RoHS and CE directive standards.

## Features and Benefits

- 3 stage control (fast/normal/float)
- Full charge with automatic shutdown
- Short circuit output protected
- Most models with 115/230 V input range
- Reverse polarity protected
- Overload protected
- UK/EU plugs
- LED indicator included
- Compliant to safety standards
- RoHS and CE directive compliant

**Specifications:**

Battery Type Charged	Lead Acid
Number of Charge Stages	3
Plug Type	UK
Standards Met	CE Certified; RoHS Compliant
User Interface	Indicator LEDs
Charge Current	25 A
Dimensions	410 x 186 x 76 mm
Input Voltage	110 to 220 V ac
Output Voltage	24 V
Output Voltage @ Charge Current	24 V at 25 A
Weight	4.9 kg
Input Frequency Range	50/60 Hz