

Angle Grinder XGT® 125 mm GA041G

Brushless, slide switch angle grinder with a 125 mm wheel for demanding professional use. Outperforming performance and efficiency similar to corded 1,000 W class grinder. AWS remote vacuum cleaner start function, and X-LOCK for quick and easy disc changes.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	9000 min ⁻¹
Disc Diameter	125 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	91 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	3,0 - 5,3 kg
Product Dimensions (L x W x H):	433 x 140 x 163 mm

User benefits

- Outperforming performance and efficiency similar to corded 1 000 W class grinder
- Excellent in continuous heavy-duty work
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Soft start for smooth start-ups

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing