



partition coupling section 3WA, frame size 1, W: 600 mm D: 400 mm

Model	
product brand name	SIVACON S4
product designation	separation 3WL size I
design of the product	coupling panel
design of the surface	zinc plated
General technical data	
design of pole	4
design	assembly kit
suitability for use	for 3WL air circuit breakers
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	2 000 mm
width	600 mm
depth	400 mm
installation width for cabinet installation	600 mm
installation depth for cabinet installation	400 mm
shape of inner subdivisions	
• shape 2a	Yes
• shape 2b	Yes
• shape 3a	Yes
• shape 3b	Yes
• shape 4a	Yes
• shape 4b	Yes
mounting position	vertical
net weight	17.7 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other



Miscellaneous



Confirmation

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-5BA12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-5BA12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-5BA12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/11/2025 

