



## **DataComm Kits**



- The IDEAL kit line offers a complete cut, strip, terminate and test solution.
- Kits offer solutions to coax and twisted pair applications.
- Different kits offer pouches, bags, or cases for easy transportation.
- Save time and money by getting all the tools in one kit instead of purchasing tools separately.



### **IDEAL DataComm**

CUT

STRIP

TERMINATE

TEST

CERTIFY

# DataComm Kit Selection Guide

Basic Data and Video Kit 33-916	Data and Video Kit 33-917	Cable Service Kit 33-605	Deluxe Cable Service Kit 33-705	Technician's Service Kit 33-505
 45-074	 45-074			
	 35-088	 35-088	 35-088	 35-088
 45-165	 45-165	 45-165	 45-165	 45-165
 45-262	 45-526			
 30-793	 30-793			
	 30-522		 30-496	
 35-485	 35-485	 35-485	 35-485	 35-485
	 35-407	 35-497	 35-497	 35-497
	 35-046		 62-200	
 35-908	 35-908	 35-905	 35-905	 35-908
	 35-473	 35-473	 35-473	 35-473
 62-140	 62-164	 62-164	 62-164	
 33-856	 33-856	 62-160	 62-160	
 35-462 (bag only)	 35-410	 35-462 (bag only)	 35-462 (bag only)	 62-205 (pouch only)

<b>Compression Connector Installation Kit 33-623</b>	<b>Economy Compression Kit 33-620</b>	<b>Service Compression Kit 33-630</b>	<b>RJ-45/11 Two, Four, Six and Eight-Position Combination TelCom Termination Kit 33-704</b>	<b>RG-6 Push-on Connector Kit 33-320</b>
 <p><b>45-074</b></p>	 <p><b>45-074</b></p>	 <p><b>45-074</b></p>		
 <p><b>45-320</b></p>	 <p><b>45-526</b></p>	 <p><b>45-262</b></p>	 <p><b>30-496</b></p>	 <p><b>45-320</b></p>
		 <p><b>LA-3953</b></p>		
 <p><b>30-633</b></p>	 <p><b>30-633</b></p>	 <p><b>30-793</b></p>		
		 <p><b>89-026</b></p>		
	 <p><b>10 Qty.</b> <b>89-054</b></p>	 <p><b>10 Qty.</b> <b>89-058</b></p>	 <p><b>15 Qty.</b> <b>85-351</b></p>	 <p><b>4 Qty.</b> <b>85-065</b></p>
	 <p><b>20 Qty.</b> <b>89-055</b></p>	 <p><b>10 Qty.</b> <b>89-057</b></p>	 <p><b>15 Qty.</b> <b>85-352</b></p>	
	 <p><b>10 Qty.</b> <b>89-056</b></p>	 <p><b>50 Qty.</b> <b>89-060</b></p>	 <p><b>15 Qty.</b> <b>85-353</b></p>	
		 <p><b>10 Qty.</b> <b>89-060P</b></p>		
 <p><b>pouch</b></p>	 <p><b>case</b></p>	 <p><b>case</b></p>	 <p><b>case</b></p>	





# Testers

## LinkMaster™ PRO XL Tester

The LinkMaster™ PRO XL Tester enables installers, contractors and maintenance technicians to map, test and troubleshoot data and voice communication cable and coax cables.

- Length measurement with test results
- Back-lighted LCD screen
- Hub Blink, Wire Map and Tone Generator



Description	Cat. No.
LinkMaster™ PRO XL Kit w/eight remotes	<b>33-880</b>
LinkMaster™ PRO XL Kit w/eight remotes & ABS™ Tester	<b>33-881</b>
LinkMaster™ PRO XL Kit w/eight remotes (international packaging)	<b>33-886</b>
LinkMaster™ PRO XL Economy Kit w/one remote	<b>33-887</b>

## VDV Multimedia Cable Tester

Easy-to-use tester for installers working with voice, data and video applications. One tester for all applications!

- **Voice** – supports 3-pair USOC and 6-position RJ-11/12 jacks for telephone cable testing
- **Data** – supports both shielded and unshielded cable testing to T568A/B (RJ-45)
- **Video** – tests coax cable for opens and shorts with F-connector interface
- Tests for opens, shorts, miswires, reversals and split pairs. Plus tone and voltage detection.



Description	Cat. No.
Kit with integrated remote and accessories	<b>33-856</b>

## SIGNALTEK™-FO Multimedia Qualification Tester

SIGNALTEK-FO is the first Qualification tester that offers both copper and fiber optic testing.

- Fiber Optic and Copper Gigabit Qualification to IEEE 802.3 standards
- Easy reporting and no software required
- Multimode and Single Mode capability – Qualify short and long range fiber cabling up to 10km
- BERT and Optical Attenuation Measurements— Perform Bit Error Rate Testing and decibel (dB) loss measurements of optical links
- Active Port Interface – DHCP, PING and ARP functions to verify set speed and connected devices



Description	Cat. No.
SIGNALTEK™-FO w/850 Modules	<b>33-981</b>
SIGNALTEK™-FO w/13X0 Modules	<b>33-982</b>
SIGNALTEK™-FO w/850 & 13X0 Modules	<b>33-983</b>
SIGNALTEK™-FO w/o Modules (Fiber-Ready)	<b>33-987</b>
SIGNALTEK™ Kit (Copper Only)	<b>33-974</b>

## SecuriTEST™ PRO CCTV/Security Tester

SecuriTEST PRO adds to the already impressive capabilities of SecuriTEST including all the features of the original, **plus IRE testing (video and sync levels), audio level testing, a high-capacity lithium ion battery in a package that's smaller and lighter than before.** The SecuriTEST PRO has all the features and functionality that CCTV technicians need to install, test, and maintain analog security camera systems. SecuriTEST PRO also includes a custom carrying case (optional with the standard SecuriTEST).



- Seven Essential CCTV Tools – Combines a CCTV video tester, PTZ camera controller, Digital Multi-Meter, UTP cable tester, video test pattern generator, PTZ protocol analyzer and camera programmer in a single compact package.
- Peak to Peak voltage (IRE) and audio level
- Save Time & Money – Test, aim, focus and program cameras when working alone. Save time by not having to walk back to the control center to verify functionality of each camera.
- PTZ Protocol Analyzer – Compatible with 20+ PTZ protocols to test and program cameras in the field. Decodes and identifies output from PTZ console to aid in troubleshooting.

Description	Cat. No.
SecuriTEST™ PRO CCTV/Security Tester and Case	<b>33-892</b>

## SecuriTEST™ CCTV/Security Tester

SecuriTEST is an affordable, all-in-one CCTV tester with all the key features installers need. The standard model operates from AA rechargeable batteries.



- Seven Essential CCTV Tools – Combines a CCTV video tester, PTZ camera controller, Digital Multi-Meter, UTP cable tester, video test pattern generator, PTZ protocol analyzer and camera programmer in a single compact package.

Description	Cat. No.
SecuriTEST™ CCTV/Security Tester only	<b>33-891</b>
SecuriTEST™ Tester Pouch only	<b>62-891</b>

## BNC Accessory Kit

All adapters required to change interface on the above test equipment from either F (CATV) or 8C Mod plug to BNC interface for coax applications.

Description	Cat. No.
BNC Accessory Kit	<b>LA-4173</b>

### IDEAL INDUSTRIES, INC.

Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:

Australia • Brazil • Canada • China • Germany • Mexico • UK

For complete sales office contact information, visit us at:

[www.idealindustries.com](http://www.idealindustries.com)