

UIC 558 22PIN SOCKET DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 022 1014
Specification	UIC 558 22PIN SOCKET DUMMY KIT
HARTING eCatalogue	https://harting.com/09580221014

Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC 558
Element	Connector sets
Specification	Dummy kit

Version

Termination method	Crimp termination
Gender	Female

Technical characteristics

Insulation resistance	$>10^7 \Omega$
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-50 ... +125 °C
Mating cycles	$\geq 10,000$
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition IP67 unmated condition & cover closed

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	RAL 7035 (light grey) RAL 5010 (gentian blue)
Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	665.37 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190382
eCl@ss	27440115 Circular connector (set)
ETIM	EC002635
UNSPSC 24.0	39121413