

Features

- 300mm length
- 18mm narrow width
- 9mm low profile design
- 12Vdc operation
- EMC (ECE R10) approved
- PIR motion sensor
- EMC (ECE R10) approved)
- 6000K cool white colour temperature
- Supplied with 300mm power cable

RS PRO Machine Lights

RS Stock No.: 0334342



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS Pro range of LED interior lighting provides excellent white lighting in 4 x different lengths (300mm, 400mm, 600mm & 900mm) and in 3 x operating functions (direct feed, on/off touch switch & PIR motion sensor).

The 18mm narrow width and 9mm low profile height are ideal for a wide range of applications.

General Specifications

Lens	Polycarbonate
Nominal flash rate	Constant
Bulb Type	LED
Light Effect	Constant
Lens Colour	Translucent
Fitting	2 x screw fix
Magnetic type	No
Multifunction	No
Number of LED	12
Special Features	White LED interior light, Low Power Consumption, 9mm Low Profile, 300mm length, EMC (ECE R10) approved
Protection	Reverse polarity protection

Electrical Specifications

Supply Voltage	12Vdc
Light Output	312 Lumen
Colour Temperature	6000K
Current Consumption	0.3A @ 12V

Mechanical Specifications

Length	300mm
Width	18mm
Height	9mm
Cable Length	300mm
Weight	0.05KG

Operation Environment Specifications

Temperature Range	-20 to +50°C
-------------------	--------------

Approvals

Compliance/Certifications	CE, UKCA, REACH
Standards Met	EMC (ECE R10), RoHS Compliant

Similar Products

Parameters	0334346	0334351	0334355
Brand	RS PRO	RS PRO	RS PRO
Lamp Type	LED Interior Light	LED Interior Light	LED Interior Light
Light Style	Steady-on	Steady-on	Steady-on
Operating Mode	PIR Motion Sensor	PIR Motion Sensor	PIR Motion Sensor
Number of LEDs	18	30	48
Lumen	442	780	1112
Voltage Rating	12Vdc	12Vdc	12Vdc
Length	400mm	600mm	900mm
Cable Length	300mm	300mm	300mm
Weight	0.06KG	0.09KG	0.13KG
Temperature Range	-20°C to +50°C	-20°C to +50°C	-20°C to +50°C